

# COLOUR SCHEME EMSA – 2014

APPROVED 10. JANUARY 2014



**Marine-blue gradient:**  
ranging left to right from Light Blue to EU Blue



|   |   |   |   |   |   |
|---|---|---|---|---|---|
| <b>EMSA Light Blue</b><br>CMYK: 70/0/0/0<br>RGB: 32/174/230 | <b>EMSA Typo Blue</b><br>CMYK: 100/30/0/0<br>RGB: 0/110/188 | <b>EU Blue CMYK:</b><br>CMYK: 100/80/0/0<br>RGB: 0/51/132 | <b>EMSA Grey</b><br>CMYK: 10/0/0/35<br>RGB: 158/168/175 | <b>EMSA Stripes</b><br>CMYK: 0/0/0/15<br>RGB: 220/220/220 | <b>Black</b><br>CMYK: 0/0/0/100<br>RGB: 0/0/0 |
|---|---|---|---|---|---|



|  |  |  |
|--|--|--|
| <b>EMSA Yellow</b><br>CMYK: 0/35/85/0<br>RGB: 243/163/28 | <b>EMSA Yellow 65%</b><br>65%: 0/35/85/0<br>RGB: 249/195/107 | <b>EMSA Yellow 35%</b><br>35%: 0/35/85/0<br>RGB: 252/223/175 |
|--|--|--|

## HORIZONTAL TASKS



|   |   |   |   |   |   |
|---|---|---|---|---|---|
| <b>EMSA Light Blue</b><br>CMYK: 70/0/0/0<br>RGB: 32/174/230 | <b>EMSA Typo Blue</b><br>CMYK: 100/30/0/0<br>RGB: 0/110/188 | <b>EU Blue CMYK:</b><br>CMYK: 100/80/0/0<br>RGB: 0/51/132 | <b>EMSA Grey</b><br>CMYK: 10/0/0/35<br>RGB: 158/168/175 | <b>EMSA Stripes</b><br>CMYK: 0/0/0/15<br>RGB: 220/220/220 | <b>Black</b><br>CMYK: 0/0/0/100<br>RGB: 0/0/0 |
|---|---|---|---|---|---|




|  |   |   |
|--|---|---|
| <b>EMSA Red</b><br>CMYK: 0/66/50/0<br>RGB: 225/94/87 | <b>EMSA Red 65%</b><br>65%: 0/66/50/0<br>RGB: 237/153/139 | <b>EMSA Red 35%</b><br>35%: 0/66/50/0<br>RGB: 246/201/189 |
|--|---|---|

## VISITS AND INSPECTIONS



|   |   |   |   |   |   |
|---|---|---|---|---|---|
| <b>EMSA Light Blue</b><br>CMYK: 70/0/0/0<br>RGB: 32/174/230 | <b>EMSA Typo Blue</b><br>CMYK: 100/30/0/0<br>RGB: 0/110/188 | <b>EU Blue CMYK:</b><br>CMYK: 100/80/0/0<br>RGB: 0/51/132 | <b>EMSA Grey</b><br>CMYK: 10/0/0/35<br>RGB: 158/168/175 | <b>EMSA Stripes</b><br>CMYK: 0/0/0/15<br>RGB: 220/220/220 | <b>Black</b><br>CMYK: 0/0/0/100<br>RGB: 0/0/0 |
|---|---|---|---|---|---|




|  |   |   |
|--|---|---|
| <b>EMSA Green</b><br>CMYK: 65/0/75/0<br>RGB: 89/166/75 | <b>EMSA Green 65%</b><br>65%: 65/0/75/0<br>RGB: 152/198/134 | <b>EMSA Green 35%</b><br>35%: 65/0/75/0<br>RGB: 202/225/190 |
|--|---|---|

## POLLUTION PREPAREDNESS, DETECTION AND RESPONSE



|   |   |   |   |   |   |
|---|---|---|---|---|---|
| <b>EMSA Light Blue</b><br>CMYK: 70/0/0/0<br>RGB: 32/174/230 | <b>EMSA Typo Blue</b><br>CMYK: 100/30/0/0<br>RGB: 0/110/188 | <b>EU Blue CMYK:</b><br>CMYK: 100/80/0/0<br>RGB: 0/51/132 | <b>EMSA Grey</b><br>CMYK: 10/0/0/35<br>RGB: 158/168/175 | <b>EMSA Stripes</b><br>CMYK: 0/0/0/15<br>RGB: 220/220/220 | <b>Black</b><br>CMYK: 0/0/0/100<br>RGB: 0/0/0 |
|---|---|---|---|---|---|



|   |  |  |
|---|--|--|
| <b>EMSA Violet</b><br>CMYK: 48/52/0/0<br>RGB: 129/110/170 | <b>EMSA Violet 65%</b><br>65%: 48/52/0/0<br>RGB: 169/157/201 | <b>EMSA Violet 35%</b><br>35%: 48/52/0/0<br>RGB: 208/201/226 |
|---|--|--|

## MARITIME SERVICES



|   |   |   |   |   |   |
|---|---|---|---|---|---|
| <b>EMSA Light Blue</b><br>CMYK: 70/0/0/0<br>RGB: 32/174/230 | <b>EMSA Typo Blue</b><br>CMYK: 100/30/0/0<br>RGB: 0/110/188 | <b>EU Blue CMYK:</b><br>CMYK: 100/80/0/0<br>RGB: 0/51/132 | <b>EMSA Grey</b><br>CMYK: 10/0/0/35<br>RGB: 158/168/175 | <b>EMSA Stripes</b><br>CMYK: 0/0/0/15<br>RGB: 220/220/220 | <b>Black</b><br>CMYK: 0/0/0/100<br>RGB: 0/0/0 |
|---|---|---|---|---|---|



|  |  |   |
|--|--|---|
| <b>EMSA Kiwi</b><br>CMYK: 37/0/100/0<br>RGB: 174/195/0 | <b>EMSA Kiwi 65%</b><br>65%: 37/0/100/0<br>RGB: 204/215/93 | <b>EMSA Kiwi 35%</b><br>35%: 37/0/100/0<br>RGB: 228/234/171 |
|--|--|---|

## TECHNICAL AND SCIENTIFIC ASSISTANCE